



EXCHANGER SIZE *BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-204-4*-4	70 5/8	1794	30 1/2	775	15	381	53	1346	8	203	8	203
WX-205-4*-4	82 5/8	2099	42 1/2	1080	27	686	65	1651	8	203	8	203
WX-206-4*-4	94 5/8	2403	54 1/2	1384	39	991	77	1956	8	203	8	203
WX-207-4*-4	106 5/8	2708	66 1/2	1689	51	1295	89	2261	8	203	8	203
WX-208-4*-4	118 5/8	3013	78 1/2	1994	63	1600	101	2565	8	203	8	203
WX-209-4*-4	130 5/8	3318	90 1/2	2299	75	1905	113	2870	8	203	8	203
WX-2010-4*-4	142 5/8	3623	102 1/2	2604	87	2210	125	3175	8	203	8	203
WX-2011-4*-4	154 5/8	3927	114 1/2	2908	99	2515	137	3480	8	203	8	203
WX-2012-4*-4	166 5/8	4232	126 1/2	3213	111	2819	149	3785	8	203	8	203
WX-2013-4*-4	178 5/8	4537	138 1/2	3518	123	3124	161	4089	8	203	8	203
WX-2014-4*-4	190 5/8	4842	150 1/2	3823	135	3429	173	4394	8	203	8	203
WX-2015-4*-4	202 5/8	5147	162 1/2	4128	147	3734	185	4699	8	203	8	203

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	6 (152) FLG
OUTLET	N2	AS PER TABLE	N6	6 (152) FLG
DRAIN	N3	1/2 (13) NPT	N7	1/2 (13) NPT
VENT	N4	3/4 (19) NPT		

NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.
 4. DRAWING IS NOT TO SCALE.
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	40 °F	4.4 °C	40 °F	4.4 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	225 PSIG	1551 KPa
CONTENTS	WATER			

CUSTOMER:
 LOCATION:
 ENGINEER:
 ORDER No.:
 PROJECT/JOB:
 LOCATION:
 TAG: (QUOTE #)

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS				A R M S T R O N G				NUMBER	WX-20-4P-4(8)	REV.
DATE:	12 / 01 / 94	BY:	D.C.R.	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.	TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491