



DIMENSIONS SHOWN AS: inches (mm)

EXCHANGER SIZE *BAFFLE SPACING	DIMENSIONS											
	A		B		C		D		N1		N2	
	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm	inches	mm
WX-62-4*-3	40 3/4	1035	28	711	19	483	39	991	3	76	3	76
WX-63-4*-3	52 3/4	1340	40	1016	31	787	51	1295	3	76	3	76
WX-64-4*-3	64 3/4	1645	52	1321	43	1092	63	1600	3	76	3	76
WX-65-4*-3	76 3/4	1950	64	1626	55	1397	75	1905	3	76	3	76
WX-66-4*-3	88 3/4	2254	76	1930	67	1702	87	2210	3	76	3	76
WX-67-4*-3	100 3/4	2559	88	2235	79	2007	99	2515	3	76	3	76
WX-68-4*-3	112 3/4	2864	100	2540	91	2311	111	2819	3	76	3	76
WX-69-4*-3	124 3/4	3169	112	2845	103	2616	123	3124	3	76	3	76
WX-610-4*-3	136 3/4	3474	124	3150	115	2921	135	3429	3	76	3	76
WX-611-4*-3	148 3/4	3778	136	3454	127	3226	147	3734	3	76	3	76
WX-612-4*-3												

NOZZLE SCHEDULE				
SERVICE	MARK	SHELL SIDE	MARK	TUBE SIDE
INLET	N1	AS PER TABLE	N5	1 1/2 (38) NPT
OUTLET	N2	AS PER TABLE	N6	1 1/2 (38) NPT
DRAIN	N3	1/2 (13) NPT	N7	1/2 (13) NPT
VENT	N4	3/4 (19) NPT		

- NOTES: 1. SUPPORTS SUPPLIED ONLY IF SPECIFIED ON ORDER.  
 2. NOZZLE SIZES SHOWN ARE RECOMMENDED FOR MAXIMUM EXCHANGER LIFE.  
 3. FABRICATED TO ASME CODE SECTION VIII DIVISION 1 AND LATEST ADDENDA.  
 4. DRAWING IS NOT TO SCALE.  
 5. ALL DIMN'S ±1/8 (3) UNLESS OTHERWISE SHOWN.

DESIGN CONDITIONS				
	SHELL		TUBES	
DESIGN PRESSURE	150 PSIG	1034 KPa	150 PSIG	1034 KPa
DESIGN TEMPERATURE	375 °F	191 °C	375 °F	191 °C
MIN. DESIGN METAL TEMP.	35 °F	1.7 °C	35 °F	1.7 °C
HYDRO. TEST PRESSURE	225 PSIG	1551 KPa	225 PSIG	1551 KPa
CONTENTS	WATER		WATER	

CUSTOMER:  
 LOCATION:  
 ENGINEER:  
 ORDER No.:  
 PROJECT/JOB:  
 LOCATION:  
 TAG: (QUOTE # )

TITLE	G.A. 150 LB. WX SERIES HEAT EXCHANGERS	A R M S T R O N G				NUMBER	WX-6-4P-3(3)	REV.	
DATE:	12 / 01 / 94	BY:	D.C.R.	TORONTO - CANADA	MONTREAL - CANADA	BUFFALO - N. Y.	COLCHESTER - U.K.		
				TEL: (416) 755-2291	TEL: (514) 421-2424	TEL: (716) 693-8813	TEL: (44) 120-657-9491		