



FILE NO: 100.111UK DATE: IANUARY 2024 SUPERSEDES: 100.111Uk DATE: JANUARY 2023



## DESIGN ENVELOPE

## ENGINEERED BEYOND THE OBVIOUS

Design Envelope technology is a demand-based, intelligent control solution that:

Models equipment and system behaviour

Monitors actual system conditions


Dynamically adjusts equipment operation to match system demand

Whether driven by social, environmental or fiscal responsibility, forwardthinking organizations must embrace energy-saving technologies and practices on their path to Net Zero. rmstrong Design
Envelope pumps are a
complete solution for
heating, cooling and plumbing
systems. The integration of a
perfectly matched hydraulics,
motive power and intelligent
control creates the highest value
pumping solution.

## MAXIMUM ENERGY AND COST SAVINGS



- Technology benefits
- How it works
- The solutions
- Armstrong services
- Solution range



#### Sizing and selecting for lowest energy consumption

Design Envelope solutions reduce pumping costs through demand-based operation — consuming only the energy required, based on current system demand. Design Envelope pumps use a combination of optimized impeller size, speed control and Active Performance Management for lowest energy use within a given performance envelope. The performance envelopes are selected for

lowest energy consumption where variable flow systems operate most often. This ensures a building's pumping system consumes as little energy as possible. It also helps to ensure that the installation meets or exceeds ASHRAE 90.1 guidelines requiring 70% energy savings at 50% of peak load.

## 1

#### **TECHNOLOGY BENEFITS**

FLOW INFORMS

he rate of fluid flow in an HVAC system is crucial to understanding how the different components are operating. Without information on system flow, it's difficult to diagnose and optimise performance. With accurate flow information, the picture changes entirely. Armstrong can optimise each component and the overall system.

Design Envelope Pumps monitor flow so accurately they function as a flow meter. Industry standards recommend balancing system flows to  $\pm 5\%$  accuracy. Design Envelope pumps deliver accuracy of  $\pm 5\%$ .

**Highly accurate and reliable:** no issues with fouling, so no need to service or re-calibrate.

Low installation cost: easy installation for retrofits.

**Integral to pump:** no additional space or wiring required.

**Energy savings:** accurate flow data informs optimisation of an entire HVAC system.


For evaluating an HVAC system, just two flow values and four temperature points provides all the data needed to understand flow rates, heat loads and operating efficiency.



PUMPING SYSTEMS








±5%

**ARMSTRONG** 

Flow 34.70 l/s

FLOW MEASUREMENT ACCURACY





## ACTIVE PERFORMANCE MANAGEMENT™


Active Performance Management is a systems management approach that optimises HVAC systems at any stage of a building's life-cycle by continually learning from a broad network of installations and responding to changing HVAC requirements.

The combination of smart commissioning with real-time alerts and system transparency addresses performance drift and maintains occupant comfort.

**Bring performance** drift under control

With Active Performance Management at the plant level, you can save up to

40% Annual cost savings



### THE **RESULTS**

**ENERGY** SAVINGS **UP TO** 





**Armstrong Design Envelope Pumps** provide you with highest energy efficiency.





**Design Envelope Pumps** provide lowest installed equipment cost, plus savings in infrastructure such as transformers, switch gear, power cables, concrete and cabling.





**Design Envelope Pumps** provide lowest operating and maintenance cost.

### CASE STUDY | National Grid



**Armstrong recently completed** a project in the United Kingdom, retrofitting pumps in a commercial office building belonging to National Grid. The retrofit included new pump sets that reduced energy consumption by 70%, saving over £22,400 annually.

#### **ANNUAL ENERGY COST**

BEFORE

**AFTER** 

32,152

9,752

AVERAGE

AVERAGE

ANNUAL

COST 22,400 £

#### CO<sub>2</sub> EMISSIONS

BEFORE

**AFTER** 

82,309

24,967

kg co<sub>2</sub> AVERAGE kg co<sub>2</sub> **AVERAGE** 

**FACILITY TYPE** Commerical



Solihull, Birmingham



ANNUAL CO2 EMISSION 57,342 kg CO2





Design Envelope Pumps provide buildings with the lowest operational and embodied carbon.






Design Envelope
Pumps provide lowest
project and operating
risk, with solutions
adaptable to design
and building changes.
It's even adaptable for
future legislation.

ogether, these five key benefits of Design Envelope technology provide customer value far beyond alternative variable-speed or constant-speed solutions.



## THE SENSOR WITHIN




Using Sensorless technology, a Design Envelope pump's performance data (power draw and RPM) and operating curve are pre-programmed into the controller. During operation, the controller monitors the power draw and RPM of the pump and establishes the hydraulic performance and position of the pump's head-flow condition relative to the system requirements.

As the building's control valves open or close to regulate flow to the cooling coils and maintain building occupant comfort, the Sensorless controller automatically adjusts to match the required system pressure and flow.

# MONITOR POWER & SPEED

# CONTROL HEAD & FLOW



## Equipped with Sensorless technology, Design Envelope solutions do not require an external sensor to monitor and control the HVAC load.

In a chilled water system, a building's temperature controls influence the local flow of control valves that modulate the flow to the cooling coils (load). As the control valves open for more chilled water flow, the differential pressure across the valve decreases.

The controller reacts to this change by increasing the pump speed. If the control valves close to reduce the chilled water flow, the differential pressure across the valve increases and the controller reduces the pump output.

## **PARALLEL SENSORLESS**

SAVE **30**%

ON OPERATING COSTS

arallel Sensorless Pump Control (PSPC) is a patented technology that improves the efficiency of a multi-pump installation through


optimised load sharing.

The traditional approach to control in a multi-pump installation involves staging pumps on the basis of motor speed. Parallel Sensorless Pump Control technology stages pumps based on operating efficiency rather than motor speed and improves the efficiency of the full pump array by up to 30% over traditional multi-pump installations.


HVAC loads and flow requirements change throughout the day. In the graphs to the right, the grey dotted line intersecting the pump efficiency curves represents the flow level at which one pump in the array should be staged on or off. The solid grey line, however, indicates where staging often occurs with speed-based control, which forces the pump array to operate at efficiency levels that are less than optimal.

In an installation of (up to four pumps) Parallel Sensorless Pump Control monitors pump speed and stages pumps at the correct flow levels to optimise efficiency, as shown in the bottom-right graph.

## TRADITIONAL SPEED-BASED STAGING




## PARALLEL SENSORLESS PUMP CONTROL BEST-EFFICIENCY STAGING



Because HVAC pumping systems mostly operate at partload, a design using two or more smaller pumps is more efficient than one larger pump. In a two-pump system, if one pump fails, the remaining pump can serve the system requirements with up to 70% flow redundancy. The capacity split can be adjusted based on the building type and duty requirement.

## REDUNDANCY AND SAVINGS WITH PARALLEL PUMPING



CAPACITY SPLIT	FLOW REDUNDANCY	DUTY REQUIREMENT	TYPICAL BUILDING EXAMPLES
Two pumps running at <b>50</b> %	If one pump fails, the other will operate at <b>70</b> %	Generic duty	Schools Apartments
Two pumps running at <b>70</b> %	If one pump fails, the other will operate at <mark>85%</mark>	High comfort sensitivity	Hotels Offices Outpatient clinics
Two pumps running at 100%	If one pump fails, the other will operate at 100%	Mission critical	Blood banks Hospitals Data centers

## (3)

#### THE SOLUTIONS

## **TANGO**

DESIGN ENVELOPE

**TECHNOLOGY** 

A DESTROY OF THE PROPERTY OF T

**Available for outdoor** 

operation

Advanced hydraulic design supports industry-leading flow efficiency

**Built-in Parallel Sensorless pump control saves up to 30% more energy** 

Armstrong DEPM motor technology delivers an additional 6-20% efficiency, meeting IE5 efficiency standards

Control algorithm constantly reviews operating conditions and adjusts output to meet immediate flow requirements at minimum energy consumption


15 minutes to replace the mechanical seal with no need for realignment, saving up to £700

#### THE NEED FOR AVAILABILITY

Most building HVAC systems operate at the design point (100% load) less than 1% of the time. Traditional system design applies 100% redundancy and duplication of components to ensure that the design point can always be met. This creates huge over capacity and higher costs.

The traditional duty/standby approach to redundancy in HVAC systems inflates the installed costs for equipment and labour, and adds to the carbon footprint of the building. Tango's dual-pumping configuration modernises the approach to redundancy. Pumps and motors are selected from a range of sizes to achieve a level of redundancy that matches the requirements of the application.

With the proper approach to redundancy, HVAC requirements can be met for all but the most extreme days of the year; and for those few days, variation in temperature will be minimal.



#### **Dual-Arm Pumps**

For pumps larger than 10hp/7.5kW use dualArm pumps for lowest installed cost, lowest life cyle operating cost achieved with Parallel Sensorless, and increased serviceability with built-in isolation valves

### FOR ALL DESIGN ENVELOPE SOLUTIONS

## Advanced performance control

Armstrong has reinvented and redesigned pumping solutions to include connectivity and performance management services. Design Envelope Pumps provide optimal lifetime efficiency through:

**Expanded performance range** (and options)

One-touch auto-flow balancing

Pump speed modulation based on an adjustable quadratic control curve for better part-load efficiency

Flow monitoring accuracy (+/- 5%)

Operating data and notifications to support diagnostics and service

**Advanced onboard control functions** 

## PERFORMANCE PACKAGES

## FUNCTIONS INCLUDED



Sensorless Bundle (standard)

- Sensorless control
- Flow meter
- Constant flow
- Constant pressure



Parallel Sensorless (standard on Tango and dualArm)

 Parallel Sensorless control



**Energy Performance Bundle** 

- Auto-flow balancing
- Maximum flow control



**Protection Bundle** 

- Minimum flow control
- Bypass valve control



**Zone optimisation** 


 Accept up to two dP sensor control signals



**Dual-season setup** 

 Pre-set heating and cooling parameters for two-pipe systems

### CASE STUDY | Delta Hotel



The Delta Hotel commissioned an upgrade of one of their existing pumps to a new Tango. New control algorithms and performance management of the Tango pump proved that the upgrade was the right choice. The total annual energy cost savings amounted to over \$2,295 with a total kWh savings of 22,957 kWh: a 40% savings overall.

#### **ANNUAL ENERGY COST**

BEFORE

**AFTER** 

5,659

3,364

\$ CAD

AVERAGE

AVERAGE

ANNUAL COST SAVINGS

\$2,295<sub>CAD</sub>

#### CO<sub>2</sub> EMISSIONS

BEFORE

AFTER

7,923 kg co<sub>2</sub>

4,709

AVERAGE

kg CO<sub>2</sub>
AVERAGE

LOCATION | Toronto, Canada





# VERTICAL IN-LINE PUMPS (VIL) OF SIGN ENVELOPE

**TECHNOLOGY** 



For a 10 hp/7.5 kW pump, save £1,500 with pipe mounting and no inertia base

#### Mechanical room space savings

Pumps require minimal floor space or can be installed overhead

#### **Reduced vibration**

Optimally-designed, dynamically-balanced impeller and shaft assembly operates with minimum vibration

## Lowest installed cost and embodied carbon

Component, Material and Labor savings: fewer fittings and no housekeeping pad required

#### **Reliability**

Vertical In-Line design requires less maintenance, at a lower cost, than any other pump configuration

#### **Easy maintenance**

15 minutes to replace the mechanical seal: no need for realignment; saves up to £500





## **AVAILABLE IN SIZES UP TO 45 KW**

35-65% lower operating costs over conventional integrated pumps

Smaller motor and controls size on 40% of hydraulic selections for lower pump and infrastructure costs

Simplified handling with single point lifting

Meets Ultra Premium (IE5) **Efficiency motor levels** 

50% weight reduction and 50% embodied carbon reduction

> **Available** for outdoor operation



### **CASE STUDY | Carlson Court**



**Armstrong replaced six** constant speed pumps with new Vertical In-Line pumps. Combining Design **Envelope technology and Pump Manager, Armstrong** optimised pump operations for annual energy savings of 87%.



SIZE 300,000 ft<sup>2</sup>

#### **ANNUAL ENERGY COST**

BEFORE

AFTER

\$140,072

\$18,380

AVERAGE

AVERAGE

cost \$121,692 cad

#### CO<sub>2</sub> EMISSIONS

BEFORE

**AFTER** 

150.847 kg co2

19,794 kg co<sub>2</sub>

AVERAGE

AVERAGE

EMISSION 131,053 kg CO2

## **END SUCTION**

DESIGN TECHNOLOGY



#### **HVAC** pumping systems are expected to operate smoothly and quietly.

Although it's practical to mount pumps on the floor, this practice can also transmit noise or vibration to the rest of the building. Concrete and inertia bases have traditionally been used to mitigate vibration, but this adds excess weight and cost to the installation.

The new Design Envelope End Suction pump with integrated vibration isolation:

#### Eliminates the need for inertia bases

**Reduces installed costs** and operating cost

Adds more value than any other horizontal pump

### **EQUIPMENT AND MATERIAL SAVINGS**

No inertia base, concrete and curing time required

Rigid pump design needs no steel baseplate

No differential pressure sensors required

Less concrete means a lower carbon footprint


Integral vibration isolation eliminates the need for inertia bases or baseplates. The following features minimise the transmission of vibration:

Balanced rotor design

Soft start controls

**Direct coupling to motor** 

Reduced overall weight



With flex connectors separating the pump from the piping, and vibration isolators between the pump and the ground, the pump floats in an isolated spring system.



The ASHRAE handbook recommends the use of inertia bases even for pump installations on grade

In pumps over 7.5 kW the integrated design with baseplate has a lower installed cost than a traditional pump with a wall-mounted drive

The vibration isolators are pre-sized for the pumping unit

## **CASE STUDY** | Texas Christian University



In 2018 Armstrong upgraded three constant-speed pumps in the Recreation Center. As a result of the retrofit project, TCU is saving over \$7,500 per year.







#### **ANNUAL ENERGY COST**

**AFTER** 

\$12,106

BEFORE

\$4,525

AVERAGE **AVERAGE** 

COST \$7,581 USD

#### CO<sub>2</sub> EMISSIONS

**BEFORE** 

AFTER

80,792 kg co2

30,193 kg co<sub>2</sub>


AVERAGE

AVERAGE

ANNUAL CO2 EMISSION 30,193 kg CO<sub>2</sub>

## CHOOSE YOUR CONFIGURATION

## INSTALLATION COST COMPARISON





	2 × End Suction with drive or and remote pressure sensor 100% duty/standby	
Total pump weigh	ht 309.3 kg	41.3 kg 87% savings
Installation weigh	nt 1007.4 kg	236.3 kg 76% savings
Installation footp	rint 2.47 m <sup>2</sup>	0.54 m <sup>2</sup> 78% savings
Installation cost	£ 7,163	£ 1,455 80% savings
	<ul> <li>Legacy design</li> <li>Base case for comparison</li> <li>Time-intensive seal change</li> </ul>	<ul> <li>Managed redundancy and parallel operation replaces duty/standby</li> <li>Smaller units are easier to handle</li> <li>Two rotating devices sharing one casing</li> <li>Reporting and proactive management</li> <li>Optimised lifetime performance</li> </ul>

## Complete integrated solutions offer the lowest installed cost and add value in lifetime energy and maintenance savings

## **DESIGN ENVELOPE CONFIGURATION OPTIONS**





2 × Design Envelope Vertical Inline with sensorless control 100% duty/standby*	2 × Design Envelope End Suction with sensorless control 100% duty/standby*
98.0 kg 68% savings	89.8 kg 71% savings
339.3 kg 66% savings	435.9 kg 57% savings
1.14 m <sup>2</sup> 54% savings	1.68 m <sup>2</sup> 32% savings
£ 3,312 54% savings	£ 3,903 46% savings
Flimington the wood few housekeeping	Fliminates the wood for

Eliminates the need for: housekeeping pads, inertia base, flex connections, grouting and alignment

- Reduced installation labour costs
- Smaller mechanical room footprint (50-75%)

#### Eliminates the need for:

housekeeping pads, inertia base, flex connections, grouting and alignment

- Reduced installation labour costs
- Smaller mechanical room footprint (50-75%)

\*May also be sized 2 × 50% parallel



### **ARMSTRONG SERVICES & PARTS**

rmstrong's 360 Service and Support provides complete solution support for engineers, contractors and owners. Working with our network partners, we provide support to help you get the best possible performance from fluid-flow systems.



Rapid response attention

MATCHED TO YOUR NEEDS.

24/7 GLOBAL RAPID RESPONSE



**ARMSTRONG PARTS KITS: ENGINEERED AND PRE-ASSEMBLED** 

rmstrong Parts Kits are engineered combinations of genuine replacement parts — planned, selected and packaged based on solution types and sizes. Use Parts Kits for maintenance projects to add value to your building operators and service personnel.



### **CASE STUDY** | Commercial Towers



ANNUAL **ENERGY** 



ANNUAL ENERGY COST

\$68,185

\$15,918

ANNUAL COST SAVINGS

\$52,267 CAD

he owners of this pair of commercial towers recently completed an HVAC upgrade, replacing three constant speed pumps with new Design Envelope pumps with Pump Manager.


Along with the energy savings, Pump Manager provided system warnings that helped avoid expensive repairs and energy losses.







### **DESIGN ENVELOPE PUMP RANGE**



PUMP MODELS
DESIGNED AND
ENGINEERED
FOR OUTDOOR
OPERATION

ıр66 rated controls enclosure

Equipped with overhead weather shield to prevent pump from icing in cold weather conditions and overheating when exposed to direct sunlight



## OUR SERVICE TO THE PLANET



## **PLANET PROPOSITION**

hrough our Planet Proposition charter, Armstrong has committed to minimising our impact on the environment. Around the world, Armstrong's Planet Proposition teams have taken on projects that are helping us meet our targets.

Two examples of successful projects are:

### NET ZERO CARBON BUILDINGS COMMITMENT

The Net Zero Commitment positions energy efficiency as a central component to achieving decarbonization globally. In signing the Net Zero Carbon Buildings Commitment, Armstrong has pledged to ensure our entire portfolio of buildings operates at net zero carbon by the year 2030.





See how we achieved a key target in reducing greenhouse gas emissions by 2 millions tons

#### TORONTO

23 BERTRAND AVENUE, TORONTO, ONTARIO, CANADA, M1L 2P3 +1 416 755 2291

#### BUFFALO

93 EAST AVENUE, NORTH TONAWANDA, NEW YORK, USA, 14120-6594 +1 716 693 8813

#### DROITWICH SPA

POINTON WAY, STONEBRIDGE CROSS BUSINESS PARK, DROITWICH SPA, WORCESTERSHIRE, UNITED KINGDOM, WR9 OLW +44 121 550 5333

#### MANCHESTER

WOLVERTON STREET, MANCHESTER UNITED KINGDOM, M11 2ET +44 161 223 2223

#### BANGALORE

#18, LEWIS WORKSPACE, 3<sup>80</sup> FLOOR, OFF MILLERS - NANDIDURGA ROAD, JAYAMAHAL CBD, BENSON TOWN, BANGALORE, INDIA 560 046 +91 80 4906 3555

#### SHANGHAI

unit 903, 888 north sichuan rd. Hongkou district, shanghai China, 200085 +86 21 5237 0909

#### BEIJING

ROOM 1612, NANYIN BUILDING NO.2 NORTH EAST THRID RING ROAD CHAOYANG DISTRICT, BEIJING, CHINA 100027 +86 21 5237 0909

#### SÃO PAULO

RUA JOSÉ SEMIÃO RODRIGUES AGOSTINHO, 1370 GALPÃO 6 EMBU DAS ARTES, SAO PAULO, BRAZIL +55 11 4785 1330

#### LYON

93 RUE DE LA VILLETTE LYON, 69003 FRANCE +33 4 26 83 78 74

#### DUBA


JAFZA VIEW 19, OFFICE 402 P.O.BOX 18226 JAFZA, DUBAI - UNITED ARAB EMIRATES +971 4 887 6775

#### JIMBOLIA

STR CALEA MOTILOR NR. 2C JIMBOLIA 305400, JUD.TIMIS ROMANIA +40 256 360 030

#### FRANKFURT

WESTERBACHSTRASSE 32, D-61476 KRONBERG IM TAUNUS GERMANY +49 6173 999 77 55



0.25 kW

Up to 932 kW available

#### **SELECT & CONFIGURE**

Use ADEPT Select to quickly and easily select
Armstrong products that are right for your projects.

Visit adept.armstrongfluidtechnology.com to learn more

ARMSTRONG FLUID TECHNOLOGY® ESTABLISHED 1934

ARMSTRONGFLUIDTECHNOLOGY.COM