

DESIGN ENVELOPE EXPRESS PUMP 4300 |

0206-005.0 | SUBMITTAL

File No: 100.3008

Date: DECEMBER 24, 2015

Supersedes: 100.3008

Date: SEPTEMBER 22, 2015

Job:	R	epresentative:	
	0	rder No:	Date:
Engineer:		ubmitted by:	Date:
Contractor:	A	pproved by:	Date:
PUMP DESIGN DATA		CONTROLS DATA	∕ ⇒EXPRESS
No. of pumps:	Tag:	Sensorless Control:	: Standard
Capacity:USgpm (L/s) Liquid:		:	: ft (m)*
Temperature: °F (°C)	Specific gravity:	Orientation:	: L1
Suction: 2" (50mm)	Discharge: 2" (50mm)	Protocol:	: BACnet TM
OSHPD Seismic Certification OSP-0422-10		Enclosure:	: Indoor - UL TYPE 12
UL STD 778 & CSA STD C22.2 NO.108 certified		емі/RFI control:	: Integrated filter designed to meet EN61800-3
MOTOR DESIGN DATA HP: 5 RPM: 3600 Frame size:	182 Enclosure: TEFC	Harmonic suppression:	: Dual DC-link reactors (Equivalent: 5% AC line reactor) Supporting IEEE 519-1992 requirements**
Volts: □ 230V □ 460V □ 575V Hertz: 60 Hz		Cooling:	: Fan-cooled through back channel
Phase: 3 Efficiency: NEMA premium 12.12 MAXIMUM PUMP OPERATING CONDITIONS ANSI 125 175 psig at 150°F (12 bars at 65°C) 100 psig at 300°F (7 bars at 150°C)		Ambient temperature:	: -10°C to +45°C up to 1000 meters above sea level (-14°F to +113°F, 3300 ft)
		Analog ı/o:	: Two current or voltage inputs, one current output
		Digital ı/o:	Six programmable inputs (two can be configured as outputs)
		Pulse inputs:	: Two programmable
ANSI 250		Relay outputs:	: Two programmable
375 psig at 150°F (26 bars at 65°C) 260 psig at 300°F (21 bars at 150°C)		Communication port:	: 1-RS485, 1-USB
		* * f	

**The IVS 102 drive is a low harmonic drive via built-in DC line reactors. This does not guaranty performance to any system wide harmonic specification or the costs to meet a system wide specification. If supplied with the system electrical details, Armstrong will run a computer simulation of the system wide harmonics. If system harmonic levels are exceeded Armstrong can also recommend additional harmonic mitigation and the costs for such mitigation.

MECHANICAL SEAL DESIGN DATA

certified dimensions


• Tolerance of ±0.125" (±3 mm) should be used

• For exact installation, data please write factory for

See file no. 43.50 for standard mechanical seal details as indicated below


Armstrong seal reference number: c1 (a)

2



Performance curves are for reference only.

Confirm current performance data with Armstrong ACE Online selection software.



TORONTO

+1 416 755 2291

BUFFALO

+1 716 693 8813

BIRMINGHAM

+44 (0) 8444 145 145

MANCHESTER

+44 (0) 8444 145 145

BANGALORE

+91 (0) 80 4906 3555

SHANGHAI

+86 21 3756 6696

ARMSTRONG FLUID TECHNOLOGY ESTABLISHED 1934

DIMENSION DATA

	INDOOR	
	(UL TYPE 12/TEFC)	
Frame size:	182	
Size:	2×2×6	
HP:	5	
RPM:	3600	
AB:	27.55(700)	
В:	4.63(118)	
c:	4.50(114)	
D:	7.00(178)	
E:	12.55(319)	
P:	10.38(264)	
F:	20.55(522)	
s:	8.00(203)	
SD:	15.00(381)	
T:	4.88(124)	
XY:	26.54(674)	
Weight:	208(94.3)	

Dimensions - inch (mm) Weight - lbs (kg)

